



Wiremold
CabinetMate Plug-In Outlet Center Unit / 120V/20A/48 long/10 O/L /6' cord/Twist Lock Plug
Part No. 4810ULBC20R-TL



Ten 20A outlets with t-slots, 6' (1.8m) cord. Length 48" (1.2m). Receptacle center-to-center 4" (101mm). 20 Amp unit with a 20A resettable circuit breaker. Units available with straight blade or Locking Plug.

Features & Benefits

Ten 20A outlets with t-slots, 6' (1.8m) cord. Length 48" (1.2m). Receptacle center-to-center 4" (101mm). 20 Amp unit with a 20A resettable circuit breaker. Units available with straight blade or Locking Plug.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776052619
Country Of Origin	Mexico	Receptacle Type	Simplex
Number of Receptacles	10	Application Sector	Commercial
Standard	cULus Recognized: File E66421 Guide XBYS XUHT VZCA	Type	PIOC

Dimensions

Product Width US	1.5 in	Product Length US	48.0 in
------------------	--------	-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant Yes

Technical Information

Phase Single Frequency Rating 60 Hz

Amperage 20 A Enclosure Type Aluminum

Mounting Type Spring Clip Voltage 125 V

Environmental Conditions Dry interior locations
