



Pass and Seymour
20A 125V Dual-Controlled Plug Load Duplex Receptacle, Gray
Part No. 5362CDGRY



Permanent controlled receptacle marking allows for long-lasting, easy identification of controlled receptacle for end-users. NEMA-approved and compliant with 2014 NEC, CA Title 24, and ASHRAE Energy Efficiency Standard 90.1.

Features & Benefits

Can be wired to any number of system-based or stand-alone plug load control solutions.	.032 inch thick, brass, triple-wipe power contacts for lasting retention.
.032 inch thick, brass, triple-wipe power contacts for lasting retention.	Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
Impact-resistant nylon face.	8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.
Tri-drive terminal and mounting screws.	Auto-ground clip assures positive ground.
For covering patents, see www.legrand.us/patents .	

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Energy Saving On/Off, Indoor	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.32 in	Product Depth US	0.78 in
------------------	---------	------------------	---------

Product Height US 2.635 in

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Amperage	20 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	Voltage	125.0 V
