



Pass and Seymour
30A 250V 15-30R Straight Blade Single Flush Receptacle, 3-Pole, 4-Wire
Part No. 5740



Straight Blade Receptacle 3-Pole 4-Wire 30A 250V

Features & Benefits

- Quality Materials.
- Durability.
- Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Application Sector	Residential/Commercial	Standard	UL 498

Dimensions

Product Width US	2.5 in	Product Depth US	2.2 in
Product Height US	3.75 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140596
cULus Listed	Yes	CSA File Number	17446

Technical Information

Number of Wires	4	Amperage	30 A
-----------------	---	----------	------

Number of Poles	3-Way	Wire Size	14 - 10 AWG
Voltage	250.0 V		