



Legrand

20A, 125V Watertight Straight Blade, Duplex Receptacle, Black
Part No. 60W33DPLX



P&S watertight receptacles feature impact-resistant Valox lids, cover plates and receptacle bodies that withstand impacts, chemical and corrosion. Ideal for the harsh environments typically found in food & beverage processing plants, petrochemical plants, marinas & shipbuilding locations, mining locations, mills and more.

Features & Benefits

Impact-resistant Valox lid, cover plate and receptacle body withstand impacts, chemicals and corrosion.

Stainless-steel hinge spring and pin ensure corrosion resistance.

For covering patents, see www.legrand.us/patents.

Spring-loaded flip cover provides protection when device is not in use.

Lockout/tagout capability.

Specifications

General Info

Color Yellow

UPC Number 785007108910

Countries Of Origin United States

Product Line Pass & Seymour

Application Sector Commercial

Standard UL Listed, CSA Listed

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Number of Poles Double Pole

Voltage 125 V

Connection Screw terminals

Dielectric Strength Connectors: 2000V AC if rated 300V or less, 3000V AC if rated above 300V. Plugs: 2500V AC if rated 300V or less, 3500V AC if rated above 300V.

Phase Single

Temperature Rating -40°C (without impact) to +60°C continuous

Wire Size #14 -#10 AWG Copper Conductor Only

Number of Wires 3

Environmental Conditions UL94 HB
