



Wiremold
CabinetMate Plug-In Outlet Center Unit / 120V/20A/70 long/11 O/L /6' cord/Twist Lock Plug
Part No. 7011ULBC20R-TL



Eleven 20A outlets with t-slots, 6' (1.8m) cord. Length 70" (1.8m). Receptacle center-to-center 6" (152mm). 20 Amp unit with a 20A resettable circuit breaker. Units available with straight blade or Locking Plug.

Features & Benefits

Eleven 20A outlets with t-slots, 6' (1.8m) cord. Length 70" (1.8m). Receptacle center-to-center 6" (152mm). 20 Amp unit with a 20A resettable circuit breaker. Units available with straight blade or Locking Plug.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776052633
Country Of Origin	Mexico	Receptacle Type	Simplex
Number of Receptacles	11	Application Sector	Commercial
Standard	cULus Recognized: File E66421 Guide XBYS XUHT VZCA	Type	PIOC

Dimensions

Product Width US	1.5 in	Product Length US	70.0 in
------------------	--------	-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Phase	Single	Frequency Rating	60 Hz
-------	--------	------------------	-------

Amperage	20 A	Enclosure Type	Aluminum
----------	------	----------------	----------

Mounting Type	Spring Clip	Voltage	125.0 V
---------------	-------------	---------	---------

Environmental Conditions	Dry interior locations
--------------------------	------------------------
