



Receptacle 4wire 20amp 120/208volt Turnlok

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

UPC Number 785007893601

Countries Of Origin Mexico

Product Line Pass & Seymour

Application Sector Industrial

Standard UL 498

Technical Information

Number of Poles 3-Way

Voltage 120 V

Phase 3

Wire Size 0-18Awg

Number of Wires 4