

Three Pole, Three Phase AC Manual Motor Controller, suitable as Motor Disconnect - 10KA @ 600VAC, 30A max. Class J Fuse.



## Features & Benefits

High Horsepower rating of 20HP

Gull-wing shaped brass terminal pressure clamps

Constructed of glass-reinforced thermoplastic

UL508 and cULus Listing of individual device and assembled device within enclosure

Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing

Two-point contact arm design reduces overall unit size

Two oversized silver alloy contacts withstand years of use; improve heat dissipation by distributing arc energy

One-piece contact carrier constructed of glassreinforced thermoplastic ensures long-lasting ""make and break"" performance

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007267686
Country Of Origin	Mexico	Standard	CSA Listed, UL Listed
Type	Manual Controller		

### Dimensions

Product Width US	1.825 in	Product Depth US	1.753 in
Product Height US	3.67 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

Technical Information

Operating Cycles	50000	Connection	Side & Back Wired
Amperage	30 A	Number of Poles	3 Pole
Wire Size	#14 - #10 AWG	Number of Phases	3
Voltage	600.0 V	Environmental Conditions	UL94 V2

---