



Pass and Seymour Manual Controller Part No. 7833MD



Three pole, Three Phase AC Manual Motor Controller 30 amp, 600 watts., Suitable as Motor Disconnect - 10KA @ 600VAC, 30A max Class J fuse.

Features & Benefits

High Horsepower rating of 20HP	Gull-wing shaped brass terminal pressure clamps
Constructed of glass-reinforced thermoplastic	UL508 and cULus Listing of individual device and assembled device within enclosure
Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing	External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals
For covering patents, see www.legrand.us/patents .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .

Specifications

General Info

Product Line	Pass & Seymour	Color	Aluminum
Country Of Origin	Mexico	Standard	CSA Listed, UL Listed

Dimensions

Product Width US	4.5 in	Product Depth US	1.8 in
Product Height US	5.75 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Operating Cycles	50000	Actuator	Toggle
Connection	Side & Back Wired	Amperage	30 A
Enclosure Type	NEMA 3R	Voltage	600.0 V
Environmental Conditions	UL94 V2		