



radiant Collection
radiant® Outdoor Outlet, Ivory
Part No. 885TRWRI



Take a step up from the standard, even outside. This weather-resistant* outlet installs easily to bring power to your patio, pool area, porch or deck, while elevating your outdoor space with the sleek, clean lines of radiant® for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Replaces any standard outlet with ease, in as little as 10 minutes.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Designed with weather-resistance for use in outdoor locations such as decks, patios and pool areas. *Must be installed in weatherproof enclosure per NEC requirements.

More color options available to fit any style.

Specifications

General Info

| | | | |
|-------------------|----------------------|-----------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Ivory |
| Country Of Origin | Mexico | Number of Receptacles | 2 |
| Outlet Type | Outdoor, Residential | Application Sector | Residential/Commercial |
| Standard | UL 498 | Warranty Type | 1-Year Limited Warranty |
| Type | Outlet | | |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 1.29 in | Product Depth US | 1.0 in |
| Product Height US | 4.2 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|-----------------|---|----------|------|
| Number of Gangs | 1 | Amperage | 15 A |
|-----------------|---|----------|------|

| Number of Poles | Double Pole | Indoor/Outdoor | Outdoor |
|-----------------|-------------|----------------|---------|
|-----------------|-------------|----------------|---------|

| | | | |
|---------------|-----|---------|-------|
| Mounting Type | Box | Voltage | 125 V |
|---------------|-----|---------|-------|