



Features & Benefits

100MHz patch cable supports 10 Gigabit Ethernet speeds

Snagless overmold prevents insertion tab from catching on other cables

UL verified to support the Cat 5e performance patch cable specification

24 AWG stranded patch cable :

Specifications

General Info

UPC Number 804428031772

Countries Of Origin Taiwan, Province Of China

Product Line On-Q

Application Sector Residential

Standard UL, CSA, FCC, 94V-0 Flame Retardant, RoHS

Dimensions

Outside Diameter < 0.25 in

Technical Information

Conductor Material Copper

Attenuation 22 dB

Plug Type RJ45 Plug

Number of Conductors 4

Wire Size 24AWG AWG