



adorne Collection
Discontinued - adorne® 1100W Incandescent/Halogen Paddle Dimmer, Magnesium, with Microban®
Part No. ADPD1103HM2



Perfect for anywhere you'd like the combined power of on/off and dimmable lighting control. Turn lights on or off with a simple rocking motion, or slide to dim to your preferred light level. Use this dimmer switch on its own to control an incandescent or halogen light or fixture from a single location, or pair with a 3-way switch to control a single light source from two locations. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

- Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Usable in both single-pole and 3-way applications.
- For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

For use with dimmable incandescent/halogen bulbs or fixtures. Features smooth paddle action for turning lights on and off, plus easy slider for adjusting lights to your preferred light level.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Country Of Origin	China	Features	Antimicrobial Protection
Switch Type	Paddle	Number of Switches	1
Standard	cULus	Warranty Type	Limited Lifetime Warranty
Type	Dimmer		

Technical Information

Connection	Screw Terminals	Number of Gangs	1
Bulb Compatibility	Halogen, Incandescent	Number of Poles	3-Way, Single Pole
Wattage	1100 W	Mounting Type	Box
Voltage	120.0 V	Connection Type	Internal Pressure Plates
Load	Incandescent, Halogen		