



Features & Benefits

Installs in 25 minutes or less, fitting into an existing electrical box and wiring directly to the light.

Self-calibrates when you select your fixture's lighting type, automatically setting the appropriate minimum voltage to eliminate flicker and poor performance.

Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Works with virtually any 120V dimmable bulb or fixture.

Pair with a Touch Wi-Fi Ready Remote Dimmer for 3-way control. Simply follow the provided instructions after installing to pair with the Master Dimmer.

Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

| | | | |
|-------------------|---|--------------------|----------------------------------|
| Product Line | Pass & Seymour | Color | White |
| Country Of Origin | United States | Features | Indicator Lights, Smart Lighting |
| Switch Type | Touch | Number of Switches | 1 |
| Works With | Amazon Alexa, Google Assistant, Radio Frequency | Application Sector | Residential |

| | | | |
|---------------------------------------|---|--------------------|---|
| Standard | cULus, FCC, UL 1472 | Warranty Type | 2-Year Limited Warranty |
| Listing Agencies / 3rd Party Agencies | | | |
| cULus Listed | Yes | FCC Compliant | Yes |
| Additional Information | | | |
| RoHS Conformant | Yes | | |
| Technical Information | | | |
| Electrical Rating | 120V 1100W (Halogen), 120V 1600VA (MLV), 120V 16A (Fluorescent), 120V 2000W (Incandescent), 120V 450W (CFL), 120V 450W (LED), 120V 5A (Fan Control), 120V 700W (ELV), 120V 8A (EFL) | Actuator | Touch |
| Frequency Rating | 900 MHz | Number of Gangs | 1 |
| Amperage | 5.5 A | Bulb Compatibility | CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon |
| Number of Poles | 3-Way, Multi-Location, Single Pole | Wattage | 700 W |
| Mounting Type | Box | Voltage | 120.0 V |
| Connection Type | Internal Pressure Plates | Load | Incandescent, Fluorescent, ELV, Halogen, CFL, LED, MLV |
| Environmental Conditions | 0 to 80% (relative humidity, non-condensing) | | |