



## Approved Networks

**Finisar FTLX8571D3BNL Compatible 10GBase-SR SFP+ Transceiver (MMF, 850nm, 300m, LC Duplex, DDM, I-Temp)**

Part No. DPC\_AN\_FTLX8571D3BNL-A

Finisar FTLX8571D3BNL Compatible 10GBase-SR SFP+ Transceiver (MMF, 850nm, 300m, LC Duplex, DDM, I-Temp)



## Features & Benefits

**Guaranteed Compatible:** In System tested in over 90 OEM switches, routers and servers. **99.98% Reliability Rate:** Functionally, optically and environmentally tested to exact specifications.

**Industry Leading Lifetime Warranty:** For more information by product line, visit our Warranty page. **98% On-Time Delivery Rate:** Extensive inventory guarantees same day shipping.

**Full Service Technical Support:** Call, chat, email or meet for expert optical connectivity support.

## Specifications

### General Info

Product Line	Approved Networks	Country Of Origin	China
Warranty Type	Lifetime	Type	Transceiver

### Dimensions

Product Width US	13.9 mm	Product Weight US	0.4 oz
Product Depth US	58.4 mm	Product Height US	13.9 mm

### Additional Information

RoHS Compliant	Yes
----------------	-----

### Technical Information

Max Distance Support	300 m	Operating Temperature Min	-40 °C
Operating Temperature Max	85 °C	Data Transfer Rate	11.1 Gbps
Connector Type	LC	Wavelength	850 nm
Form Factor	SFP+		