



## Approved Networks

**Finisar FTLX8574D3BCL Compatible 10GBase-SR SFP+ Transceiver (MMF, 850nm, 300m, LC Duplex, DDM, I-Temp)**

Part No. DPC\_AN\_FTLX8574D3BCL-A

Finisar FTLX8574D3BCL Compatible 10GBase-SR SFP+ Transceiver (MMF, 850nm, 300m, LC Duplex, DDM, I-Temp)



## Features & Benefits

**Guaranteed Compatible:** In System tested in over 90 OEM switches, routers and servers. **99.98% Reliability Rate:** Functionally, optically and environmentally tested to exact specifications.

**Industry Leading Lifetime Warranty:** For more information by product line, visit our Warranty page. **98% On-Time Delivery Rate:** Extensive inventory guarantees same day shipping.

**Full Service Technical Support:** Call, chat, email or meet for expert optical connectivity support.

## Specifications

### General Info

|               |                   |                   |             |
|---------------|-------------------|-------------------|-------------|
| Product Line  | Approved Networks | Country Of Origin | China       |
| Warranty Type | Lifetime          | Type              | Transceiver |

### Dimensions

|                  |         |                   |         |
|------------------|---------|-------------------|---------|
| Product Width US | 13.9 mm | Product Weight US | 0.4 oz  |
| Product Depth US | 58.4 mm | Product Height US | 13.9 mm |

### Additional Information

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

### Technical Information

|                           |       |                           |           |
|---------------------------|-------|---------------------------|-----------|
| Max Distance Support      | 300 m | Operating Temperature Min | -40 °C    |
| Operating Temperature Max | 85 °C | Data Transfer Rate        | 11.1 Gbps |
| Connector Type            | LC    | Wavelength                | 850 nm    |
| Form Factor               | SFP+  |                           |           |