



Approved Networks

Finisar FTLX8574D3BNL Compatible 10GBase-SR SFP+ Transceiver (MMF, 850nm, 300m, LC Duplex, DDM, I-Temp)

Part No. DPC_AN_FTLX8574D3BNL-A

Finisar FTLX8574D3BNL Compatible 10GBase-SR SFP+ Transceiver (MMF, 850nm, 300m, LC Duplex, DDM, I-Temp)



Features & Benefits

Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers. **99.98% Reliability Rate:** Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page. **98% On-Time Delivery Rate:** Extensive inventory guarantees same day shipping.

Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

Specifications

General Info

Product Line	Approved Networks	Country Of Origin	China
Warranty Type	Lifetime	Type	Transceiver

Dimensions

Product Width US	13.9 mm	Product Weight US	0.4 oz
Product Depth US	58.4 mm	Product Height US	13.9 mm

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Max Distance Support	300 m	Operating Temperature Min	-40 °C
Operating Temperature Max	85 °C	Data Transfer Rate	11.1 Gbps
Connector Type	LC	Wavelength	850 nm
Form Factor	SFP+		