



Approved Networks
Dell Q28-100G-LR4 Compatible 100GBase-LR4 QSFP28 Transceiver (SMF, 1295.56nm:1300.05nm:1304.58nm:1309.14nm, 10km, LC Duplex, DDM, C-Temp)
Part No. DPC_AN_Q28-100G-LR4-A

Dell Q28-100G-LR4 Compatible 100GBase-LR4 QSFP28 Transceiver (SMF, 1295.56nm:1300.05nm:1304.58nm:1309.14nm, 10km, LC Duplex, DDM, C-Temp)



Features & Benefits

Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.

99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

Specifications

General Info

Product Line	Approved Networks	Country Of Origin	China
Warranty Type	Lifetime	Type	Transceiver

Dimensions

Product Width US	18.8 mm	Product Weight US	0.4 oz
Product Depth US	123.21 mm	Product Height US	11.68 mm

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Max Distance Support	10 km	Operating Temperature Min	0 °C
Operating Temperature Max	70 °C	Data Transfer Rate	103.1 Gbps
Connector Type	LC	Wavelength	1295 - 1309 nm
Form Factor	QSFP28		