



## Approved Networks

**Juniper QFX-SFP-1GE-T Compatible 10/100/1000Base-TX SFP Transceiver (Copper, 100m, RJ-45, Non-DDM, C-Temp)**

Part No. DPC\_AN\_QFX-SFP-1GE-T-A

Juniper QFX-SFP-1GE-T Compatible 10/100/1000Base-TX SFP Transceiver (Copper, 100m, RJ-45, Non-DDM, C-Temp)



## Features & Benefits

**Guaranteed Compatible:** In System tested in over 90 OEM switches, routers and servers. **99.98% Reliability Rate:** Functionally, optically and environmentally tested to exact specifications.

**Industry Leading Lifetime Warranty:** For more information by product line, visit our Warranty page. **98% On-Time Delivery Rate:** Extensive inventory guarantees same day shipping.

**Full Service Technical Support:** Call, chat, email or meet for expert optical connectivity support.

## Specifications

### General Info

Product Line	Approved Networks	Country Of Origin	China
Warranty Type	Lifetime	Type	Transceiver

### Dimensions

Product Width US	13.66 mm	Product Weight US	0.4 oz
Product Depth US	80.77 mm	Product Height US	13.97 mm

### Additional Information

RoHS Compliant	Yes
----------------	-----

### Technical Information

Max Distance Support	100 m	Operating Temperature Min	-40 °C
Operating Temperature Max	85 °C	Data Transfer Rate	1.25 Gbps
Connector Type	RJ45	Form Factor	SFP-T