




adorne Collection
adorne® 20A 4-Way Paddle Switch, Graphite, with Microban®
Part No. ASPD2042G4



Gain control of a single light from even more locations with this 4-way 20A switch. Updating the classic up-and-down switch with sleek paddle control, this modern light switch lets you turn lights on and off with ease and style. Must be paired with additional switches to provide control from multiple locations.

This switch* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Combine with other switches or dimmers in 4-way applications, allowing control of a single light source from multiple locations.

Specifications

General Info

Product Line	Pass & Seymour	Color	Graphite
Country Of Origin	Mexico	Features	Antimicrobial Protection
Switch Type	Paddle	Number of Switches	1
Warranty Type	Limited Lifetime Warranty		

Dimensions

Product Width US	1.77 in	Product Depth US	1.72 in
Product Height US	1.77 in		

Technical Information

Number of Gangs	1	Amperage	20 A
Number of Poles	4-Way, Single Pole	Mounting Type	Box
Voltage	120.0 V	Connection Type	Internal Pressure Plates