



adorne Collection  
**Discontinued - adorne® Whisper™ Wi-Fi Ready Master Switch, Magnesium**  
Part No. ASWR155RMM1



The Whisper Wi-Fi Ready Master Switch pairs with the adorne Hub to create a smart Wi-Fi Lighting Control System for your home. Manually turn lights on/off with a light fluid motion at the wall, or enjoy mobile control and create custom lighting scenes to control lights through the Legrand Lighting Control app for smartphones or tablets. For 3-way, or multi-way applications, use one master device with additional remote devices. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

- Installs in 25 minutes or less, fitting into an existing electrical box and wiring directly to the light.
- Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.
- Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate.
- Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.
- Pair with a Whisper Wi-Fi Ready Remote Switch for 3-way control.
- Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.
- More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Magnesium
Country Of Origin	China	Features	Smart Lighting
Switch Type	Whisper	Number of Switches	1
Works With	Amazon Alexa, Google Assistant, Radio Frequency	Application Sector	Residential
Standard	UL, FCC, cULus, RoHS	Warranty Type	1-Year Limited Warranty

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Number of Gangs	1	Number of Poles	4-Way, Multi-Location, Single Pole
Mounting Type	Box	Supply Voltage	120 V
Voltage	120.0 V	Connection Type	Internal Pressure Plates
Environmental Conditions	0 to 80% (relative humidity, non-condensing)		