



On-Q
9-inch Dual-Purpose In-Wall Enclosure with 5-inch Mounting Plate
Part No. ENP0905NAV1



The 9-inch Dual-Purpose In-Wall Enclosure is engineered to provide storage of structured wiring and AV components. The ENP0905NAV1 is constructed of Wi-Fi transparent material to manage wireless components and AV devices at point-of-use locations, like directly behind a TV or other media centers. It can also be used for structured wiring purposes, such as networking equipment, access points, switches and more. The ENP0905NAV1 is compatible with devices like Apple TV, Roku, Amazon Fire TV, network switches, 3rd party structured wiring components and more. Includes a 5-inch elevated mounting plate, cover, trim ring and drywall clips, allowing for both new construction and retrofit installations.

Features & Benefits

| | |
|--|---|
| Replacement trim ring and cover | Can be placed behind most TV wall-mounts including SANUS premium TV mounts |
| Compatible with devices like Apple TV, Roku, Amazon Fire TV, network switches, 3rd party structured wiring components and more | Comes with removable mounting plate that features 1.5-in of elevation to accommodate larger devices and frees up space in the enclosure |
| Tool-free cover is low profile and designed to snap into place providing a "flush" appearance to wall surface | Knockout configurations support conduit and in-wall wired connections, while a cable pass through on cover allows for outside cable connections |
| Features (2) AC knockouts to accommodate a single gang junction box to power devices in enclosure | Universal mounting grid maximizes compatibility with 3rd party devices without additional mounting brackets |
| Features drywall clips to allow both retrofit and new construction installations | UL Listed and constructed of Wi-Fi transparent ABS plastic to ensure uninterrupted performance of wireless devices |
| Proudly made in the USA | |

Specifications

General Info

| | | | |
|------------------|-----------------|--------------------|------------------------|
| Product Line | On-Q | Color | White |
| UPC Number | 804428434139 | Country Of Origin | United States |
| Package Quantity | 5 | Application Sector | Residential/Commercial |
| Standard | RoHS, UL, cULus | Type | Enclosure |

Dimensions

| | | | |
|---------------------------------------|---|------------------|--|
| Product Width US | 14.37 in | Product Depth US | 3.88 in |
| Product Height US | 9.33 in | | |
| Listing Agencies / 3rd Party Agencies | | | |
| cULus Listed | Yes | | |
| Additional Information | | | |
| RoHS Conformant | Yes | | |
| Technical Information | | | |
| Compatibility | Paintable with Rust-Oleum paint for plastic or equivalent | Thickness | 0.1 in |
| Enclosure Type | Dual Purpose | Frame | Injection-molded plastic |
| Operating Temperature | 32°-122°F | Mounting | Consult the Factory for Mounting Recommendations |
| Environmental Conditions | 0 to 93% (relative humidity, non-condensing) | | |