



Stainless Steel, Standard duty, Split rod, Single eye. Cable diameter - 2.000-2.490", Bale length - 16", Mesh length - 22", Break strength - 3,760 lbs.

Features & Benefits

Split rod support grips are designed for loads up to 600 lbs.

Vertical runs of no more than 100 ft.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Split rod support grips are used when the end of the cable cannot be easily accessed and the installation is temporary.

Support grips are woven of corrosion-resistant stainless steel wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	FR200U
Country Of Origin	Mexico		