



Wattstopper
0-10V PIR DROP MT SENSOR BLE 1 20-277V - 40FT LENS - BRONZE
Part No. FSP-311B-D-L7-BR



The FSP-3x1B sensors provide continuous dimming light level control based on motion and/or daylight contribution. They control 0-10 VDC LED drivers or dimming ballasts, as well as non-dimming ballasts and, with an FSP-Lx Lens, are rated for wet and cold locations. All control parameters are adjustable via the iOS or Android Sensor Configuration App capable of storing and transmitting sensor profiles. The FSP-3x1B family is available in three configurations for mounting inside a fixture, to the outside of a fixture via a 1/2" knockout, or to a pole.

Features & Benefits

Designed for LED fixtures and rated for extreme temperatures; options for box or pole mounting

Fully adjustable high and low dimmed light levels

Hold off setpoint with automatic calibration option for convenience and added energy savings

Continuous dimming & daylight harvesting for energy efficiency and energy code compliance

Adjustable via the iOS® or Android® Sensor Configuration App

IP66 rated with choice of lenses for wet and outdoor locations, and mounting heights from 8' to 40'

Adjustable time delay and cutoff delay

Specifications

General Info

Product Line	Wattstopper	UPC Number	754182941322
Country Of Origin	China		

Dimensions

Product Width US	5.0 in	Product Weight US	0.5 lb
Product Volume US	105.0 cu in	Product Depth US	7.0 in
Product Height US	3.0 in		

Technical Information

Sensor Type	Daylight, Occupancy
-------------	---------------------