



Wattstopper
0-10V PIR DROP MT SENSOR BLE 1 20-480V 10FT LENS - BRONZE
Part No. FSP-321B-D-L2-BR



The FSP-3x1B sensors provide continuous dimming light level control based on motion and/or daylight contribution. They control 0-10 VDC LED drivers or dimming ballasts, as well as non-dimming ballasts and, with an FSP-Lx Lens, are rated for wet and cold locations. All control parameters are adjustable via the iOS or Android Sensor Configuration App capable of storing and transmitting sensor profiles. The FSP-3x1B family is available in three configurations for mounting inside a fixture, to the outside of a fixture via a 1/2" knockout, or to a pole.

Features & Benefits

| | |
|--|---|
| Designed for LED fixtures and rated for extreme temperatures; options for box or pole mounting | Fully adjustable high and low dimmed light levels |
| Hold off setpoint with automatic calibration option for convenience and added energy savings | Continuous dimming & daylight harvesting for energy efficiency and energy code compliance |
| Adjustable via the iOS® or Android® Sensor Configuration App | IP66 rated with choice of lenses for wet and outdoor locations, and mounting heights from 8' to 40' |
| Adjustable time delay and cutoff delay | |

Specifications

General Info

| | | | |
|-------------------|-------------|------------|--------------|
| Product Line | Wattstopper | UPC Number | 754182941483 |
| Country Of Origin | China | | |

Dimensions

| | | | |
|-------------------|-------------|-------------------|---------|
| Product Width US | 6.0 in | Product Weight US | 0.44 lb |
| Product Volume US | 39.69 cu in | Product Depth US | 6.3 in |
| Product Height US | 1.0 in | | |

Technical Information

| | |
|-------------|---------------------|
| Sensor Type | Daylight, Occupancy |
|-------------|---------------------|