



**Wattstopper**  
**0-10V PIR STRAIGHT MT SENSOR BLE 120-480V 20FT LENS -BRONZE**  
Part No. FSP-321B-S-L3-G



The FSP-3x1B sensors provide continuous dimming light level control based on motion and/or daylight contribution. They control 0-10 VDC LED drivers or dimming ballasts, as well as non-dimming ballasts and, with an FSP-Lx Lens, are rated for wet and cold locations. All control parameters are adjustable via the iOS or Android Sensor Configuration App capable of storing and transmitting sensor profiles. The FSP-3x1B family is available in three configurations for mounting inside a fixture, to the outside of a fixture via a 1/2" knockout, or to a pole.

## Features & Benefits

Designed for LED fixtures and rated for extreme temperatures; options for box or pole mounting	Fully adjustable high and low dimmed light levels
Hold off setpoint with automatic calibration option for convenience and added energy savings	Continuous dimming & daylight harvesting for energy efficiency and energy code compliance
Adjustable via the iOS® or Android® Sensor Configuration App	IP66 rated with choice of lenses for wet and outdoor locations, and mounting heights from 8' to 40'
Adjustable time delay and cutoff delay	

## Specifications

### General Info

Product Line	Wattstopper	Color	Gray
UPC Number	754182941650	Country Of Origin	China

### Dimensions

Product Width US	6.0 in	Product Weight US	0.44 lb
Product Volume US	39.69 cu in	Product Depth US	6.3 in
Product Height US	1.0 in		

### Additional Information

RoHS Conformant	Yes	Security	Yes
-----------------	-----	----------	-----

---

Technical Information

---

Sensor Type	Daylight, Occupancy
-------------	---------------------

---