



Wiremold  
Rack Mount 120V/15A/8 rear O/L /lighted switch/6' cord  
Part No. J08B0B



Eight rear outlets, lighted switch, 15A, receptacles rotated 90 degrees and 4 outlets spaced to accommodate transformers. 6' (1.8m) cord. Receptacle center-to-center 1 1/2" (38mm) and 2" (51mm).

## Features & Benefits

Eight rear outlets, lighted switch, 15A, receptacles rotated 90 degrees and 4 outlets spaced to accommodate transformers. 6' (1.8m) cord. Receptacle center-to-center 1 1/2" (38mm) and 2" (51mm).

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776012187
Country Of Origin	China	Receptacle Type	Simplex
Number of Receptacles	8	Application Sector	Commercial
Standard	cULus Recognized: File E66421, Guide XBYS2 XUHT2 VZCA2	Type	PIOC

### Dimensions

Product Width US	1.75 in	Product Depth US	2.57 in
Product Length US	19.0 in		

### Additional Information

RoHS Conformant	Yes
-----------------	-----

### Technical Information

Phase	Single	Frequency Rating	60 Hz
Amperage	15 A	Enclosure Type	Steel
Mounting Type	Rack Mounting	Voltage	125.0 V
Environmental Conditions	Dry interior locations		