



Pass and Seymour
Stainless Steel Liquid-Tight Connector, 1-in 90-Degree
Part No. LTB10090SS



Rated IP68 and NEMA 4X, Stainless Steel Liquid-Tight Connectors offer corrosion resistance for the toughest environments. For use in wet or dry locations to seal electrical connections against dust, dirt, oil, water, chemicals and other corrosive elements. These are available in straight and 90 degree, 3/8" to 2" NPT. The stainless steel liquid-tight offering includes a nylon-insulated throat and Viton O-Ring.

Features & Benefits

304 grade stainless steel construction resists corrosion and impacts

Includes a nylon-insulated throat and embedded Viton: O-Ring to ensure a watertight seal

Rated IP68 and NEMA 4X for use in wet or dry locations to seal electrical connections against dust, dirt, oil, water, chemicals and other corrosive elements

Available in straight and 90: , 3/8" to 2"

Stainless Steel Liquid-Tight Connectors are ideally suited for OEM and MRO applications known for their corrosive and abusive environments

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007109856
Country Of Origin	United States		