



Infinium Quantum Splice Cassettes are available in the Infinium M4 footprint, enabling industry leading performance, fast field termination, and providing cable management within the housing. The Splice Cassettes are designed for use with Single-Mode (OS2) or Multimode (OM4/OM5) Fiber, Houses 12-24 fibers and are available in LC Duplex or LC Quad port configurations.

The 12 fiber cassettes and support fusion splicing of individual fibers, while the 24 fiber cassettes support fusion splicing of ribbon fibers. Heat shrinks, pigtail slack and cable slack are managed within the cassette—eliminating the need for individual splice trays or housings. The design of the cassettes allows easy mounting from either the front or the rear of an enclosure or panel, and individual fibers within the cassette may be accessed without disturbing the other fibers in the housing

Specifications

General Info

Product Line	Ortronics	Color	Black
Country Of Origin	United States	Included	(12 or 24) Fiber Pigtails, Adapter Panel, Protective Dust Caps, Splice Management Tray, Splice Protection Sleeves
Standard	TIA-568-C.3	Type	Cassette

Dimensions

Product Width US	3.45 in	Product Depth US	4.77 in
Product Height US	1.14 in		

Technical Information

Compatibility	Infinium HD-E / Infinium Panel	Number of Ports	24
Connector Type	LC Quad	Performance Level/Tier	Infinium Quantum