



Sentrex high performance surge protection. Five outlets, lighted switch, durable putty white aluminum housing, 15A. Receptacles rotated 90 degrees and spaced to accommodate transformers. Length 24" (610mm). 6' (1.8m) 14/3 SJT putty white cord with NEMA5-15 plug. Snap-on, slide-off mounting.

### Features & Benefits

Sentrex high performance surge protection. Five outlets, lighted switch, durable putty white aluminum housing, 15A. Receptacles rotated 90 degrees and spaced to accommodate transformers. Length 24" (610mm). 6' (1.8m) 14/3 SJT putty white cord with NEMA5-15 plug. Snap-on, slide-off mounting.

### Specifications

#### General Info

Product Line	Wiremold	UPC Number	786776044119
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Type	PIOC

#### Dimensions

Product Width US	23.81 in	Product Height US	1.89 in
Product Length US	2.0 in		

#### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

#### Buy American Act Compliance

NAFTA	Yes
-------	-----

#### Technical Information

Phase	3-Stage Hybrid Circuit, 3 Element	Frequency Rating	+50dB Hz
Connection	Cord-ended	Class	75
Amperage	15 A	Short Circuit Rating	56000 Amps [32000 Amps L-N 12000 Amps L-G 12000 Amps N-G]
Response Time	<1 ns	Mounting Type	Slide-off, Snap-on

Mounting	Yes	Type of Indicators	Light
Voltage	120.0 V	Environmental Conditions	Indoor, dry location