



Nuvo
Discontinued - 6.5-in Series Six Outdoor Speaker, Black
Part No. NV6OD6BK



Fill your outdoor space with crystal-clear, powerful audio using the Nuvo Series Six 6.5" Outdoor Speaker. Offering the highest power handling and performance, this speaker is designed with a 6.5" combination carbon fiber/Kevlar woofer and a 1" titanium tweeter for the ultimate listening experience. The sleek enclosure boasts a modern form and minimal size that tastefully blend with the lines of any home.

Optimized for the demands of outdoor installations, the Outdoor Speakers are IP65 and MIL-STD- 810 rated. Designed for easy installation, the speaker safely rests on the bracket with mounting knobs loosely installed to allow flexibility while wiring the removable phoenix connector. After the terminal has been secured, simply adjust the angle, tighten knobs, install covers, and mounting is complete.

Features & Benefits

| | |
|--|---|
| 8 ohm rated | Aluminum powder coated grill |
| Aluminum speaker bracket | Designed for safe and easy installation |
| Fill your outdoor space with crystal-clear, powerful audio | IP65 Rated for outdoor use and MIL-STD-810 for UV, salt spray, and temperature extremes |
| Lifetime Warranty | Single stereo speaker is ideal when space is limited or two speakers aren't required |
| Output Wattage of 12.9 - 15.6 | |

Specifications

General Info

| | | | |
|-------------------|---|--------------------|--------------|
| Product Line | Nuvo | UPC Number | 701963859758 |
| Country Of Origin | China | Application Sector | Residential |
| Standard | CE, RoHS, REACH Compliant, #ABS and #4 PELD Recyclable, IP65, MIL 810 | | |

Technical Information

| | | | |
|-----------------|--------|---------------------|---------------------------------|
| Woofer Diameter | 6.5 in | Tweeter Composition | Titanium Pivoting Dome Tweeters |
|-----------------|--------|---------------------|---------------------------------|

| | | | |
|--------------------|-----------------------------|------------|---------------|
| Frequency Response | 55 to 20 KHz | Efficiency | 89 dB |
| IP Control | IP65 and MIL-STD- 810 rated | Impedance | 8.0 ohms |
| Woofer Composition | Poly | Mounting | Outside Mount |
| Tweeter Diameter | 0.5 in | | |