



Cablofil  
DS-8936-01-S6 M10 x 30mm HEX HEAD BOLT  
Part No. P081400



Finishes include steel and 316L stainless steel to meet the needs of any application. Rail heights range from 4" to 7".

## Features & Benefits

All splices are supplied in pairs.

Geomet fasteners are standard on aluminum and steel cable tray systems.

Type 316 stainless steel fasteners are standard on stainless steel systems, but are available as an option on all aluminum and steel systems.

Sufficient connector pairs with fasteners are automatically included with each shipment of straight sections and fittings. Extras for field cuts or spares must be ordered separately.

Bonding jumpers are required for all expansion splice plates, adjustable connectors, and tray discontinuities.

## Specifications

### General Info

Product Line	Cablofil	Finish	Stainless 316
UPC Number	800388514157	Country Of Origin	China

### Dimensions

Product Width US	0.67 in	Product Weight US	0.06 lb
Product Depth US	1.433 in	Product Height US	0.75 in