



Cablofil  
7" Itray Aluminum Straight Sections  
Part No. P302145



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

## Features & Benefits

Material: Aluminum Alloy 6063-T6

Finish: Plain

Bottom: Ldr: 1" wide I rung SB: Flat Sheet over 12" Rung Spacing.  
SC: Solid Corrugated VC: Vented Corrugated

Construction: Welded

Tray Design: Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126.

Tray Grounding Capability: Classified as an equipment grounding conductor per NEC 392.60.

## Specifications

### General Info

|              |              |                   |        |
|--------------|--------------|-------------------|--------|
| Product Line | Cablofil     | Finish            | AL     |
| UPC Number   | 800388080102 | Country Of Origin | Mexico |

### Dimensions

|                   |              |                   |           |
|-------------------|--------------|-------------------|-----------|
| Product Width US  | 10.5 in      | Product Weight US | 71.544 lb |
| Product Volume US | 12.705 cu ft | Product Depth US  | 288.0 in  |
| Product Height US | 7.26 in      |                   |           |

### Buy American Act Compliance

|     |     |
|-----|-----|
| BAA | Yes |
|-----|-----|