



Pass and Seymour
65W Commercial USB Outlet, Type C, 20A, Tamper-Resistant, Black
Part No. EWS_PS_TR20USBP65BK



Elevate the power and convenience in your commercial spaces with Legrand's 65W USB Outlet, equipped with dual Type-C ports and Power Delivery for high-capacity charging. Designed for safe, efficient charging of essential devices – including smartphones, tablets, and small laptops like the 13-inch MacBook Pro and Chromebooks – this outlet provides an industry-leading power solution tailored for the future of commercial power needs.

Features & Benefits

Charges the latest electronics, including small laptops like the 13-in MacBook Pro, Chromebooks, and Microsoft Surface Pro 9 thanks to industry-leading amperage and 65W of power courtesy of advanced Power Delivery

Built for intelligent charging, the outlet detects and delivers the precise amount of power needed to maximize charging speeds

Provides fast and convenient built-in charging through two USB Type-C ports, accommodating modern devices without an adapter

Helpful indicator light lets you see charging status at a glance. Light glows yellow while charging is in progress, and shows green once the device battery is 90% charged

Includes multiple layers of overcurrent protection, ensuring the outlet and devices can charge at optimal levels in high traffic settings

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Limited Lifetime Warranty

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect

Simple and easy to wire lead reduces installation time

More color options available to fit any style or space

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007460940	Number of Receptacles	2
Features	Indicator Lights, USB-C Charging	Outlet Type	Tamper-Resistant, USB
Application Sector	Commercial, Education, Hospitality, Industrial	Wall Plate Included	No

Standard	cULus, UL	Warranty Type	Limited Lifetime Warranty
Dimensions			
Product Width US	2.99 in	Product Weight US	0.422 lb
Product Depth US	1.52 in	Product Height US	1.94 in
Product Length US	4.88 in		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Operating Temperature Min	-40 °C	USB Wattage	65 W
Number of USBs	2	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-20R	Operating Temperature	-40°-60°C
Wire Connection Type	Wire Leads	Voltage	15.0 V, 5.0 V, 9.0 V