



Pass and Seymour  
**TradeMaster Residential Single Outlet, 20amp, White**  
Part No. EWS\_PS\_TR53201W



The TradeMaster Residential Single Outlet is designed for use as a dedicated outlet for small appliances like microwaves and refrigerators. Built with patented 'invisi-shutters,' the tamper-resistant outlet safely protects against the potential insertion of foreign objects. The single receptacle is equipped for heavy-duty use in residential applications, with a PVC face material and corrosion-resistant through strap. Pair this outlet with TradeMaster unbreakable wall plates to complete the job.

## Features & Benefits

Rated for safe use as a dedicated outlet for small appliances like microwaves and refrigerators

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Built with PVC face material

Corrosion-resistant through strap

Available in 15A and 20A options

Recommended use with the TradeMaster unbreakable wall plates

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007454710
Number of Receptacles	1	Outlet Type	Tamper-Resistant
Application Sector	Residential	Wall Plate Included	No
Warranty Type	1-Year		

### Dimensions

Product Width US	1.3 in	Product Weight US	1.38 lb
Product Depth US	1.03 in	Product Length US	4.2 in

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

### Technical Information

---

Operating Temperature Min	-40 °C	Connection Location	Side Only
---------------------------	--------	---------------------	-----------

---

Flanged	Yes	Terminal Accommodation	#14 AWG - #10 AWG
---------	-----	------------------------	-------------------

---

Number of USBs	0	Number of Wires	3
----------------	---	-----------------	---

---

Operating Temperature Max	60 °C	Amperage	20 A
---------------------------	-------	----------	------

---

Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20R
----------------	--------	-------------------------	-------

---

Operating Temperature	-40°-60°C	Wire Connection Type	Screw Terminal
-----------------------	-----------	----------------------	----------------

---

Voltage	125.0 V
---------	---------

---