



Pass and Seymour
Replacement Cover for Standard Switch, 30A
Part No. PS30SSRC

Replacement cover for use with Non-Fusible Safivety Switch PS30SS.

Product Image Coming

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	United States	Application Sector	Industrial
Standard	UL, CSA		

Dimensions

Product Width US	4.9 in	Product Depth US	6.52 in
Product Height US	8.4 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Contact Configuration	[Optional] 1 N.O. & 1 N.C.	Contact Rating	(Optional) 10A @ 600VAC
Amperage	30 A	Voltage	600.0 V

Environmental Conditions

Moisture Resistance: Per UL50, Section 35, NEMA
Enclosure Type 4X (watertight, hosedown), Type
12K (dusttight, falling dirt), and IP67 suitability:
Flammability: UL94 5VA and V0 Classification: UV
Resistance: All enclosure materials are UV stable
