



Pass and Seymour
60A 2 Pole 3 Wire Fusible Mechanical Interlock
Part No. PS360FMIR6W



Two pole, Three wire, Fusible Mechanical Interlock Receptacle. 1.5 HP Standard 7.5 HP Max, 240VAC

Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	United States		

Dimensions

Product Width US	9.13 in	Product Depth US	9.94 in
Product Height US	24.5 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Amperage	60 A
----------	------