



Pass and Seymour
Series 16 Protective Caps and Adapters
Part No. PSFFCBK

CAM TYPE FMALE TO FMALE COUPLER BK



Features & Benefits

Quality Materials, durability, and time-tested design

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|-----------------------|
| Product Line | Pass & Seymour | Color | Black |
| Country Of Origin | Mexico | Application Sector | Commercial/Industrial |
| Standard | cCSAus | | |

Technical Information

| | | | |
|----------|---------|--------------------------|---|
| Amperage | 400 A | Wire Size | 2/0 - 4/0 |
| Voltage | 600.0 V | Environmental Conditions | Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4 |