



Pass and Seymour
PlugTail® Three-Way 15A Toggle Switch, Light Almond
Part No. PT15AC3LA



PlugTail® 3-way 15A Toggle Switch

Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Shallow design for easier installation.

No exposed terminals create a finger-safe application before, during, and after installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Impact- and chemical- resistant cover.

One-piece nickel-plated mounting strap for superior corrosion resistance.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|--------------------|------------------------|-------------------|--------|
| Product Line | Pass & Seymour | Country Of Origin | Mexico |
| Application Sector | Residential/Commercial | Standard | UL 20 |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|-----------------|-------------|----------------|-------------------|
| Actuator | Toggle | Contact Rating | 120/277vac, 15amp |
| Amperage | 15 A | Action | DPDT |
| Number of Poles | Double Pole | Voltage | 120.0 V |