



Pass and Seymour
PlugTail® Heavy Duty Spec Grade Plug Load Controllable Receptacle, 15A, 125V, Gray
 Part No. PT26252CDGRY



These durable, dependable receptacles feature a permanently marked, differentiated solution that meets all necessary code requirements. For detailed PlugTail® information, visit our PlugTail® Headquarters.

Features & Benefits

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Plated steel wrap strap design for maximum durability and corrosion resistance.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Dual mechanical shutter system to help prevent insertion of foreign objects (TR models).

Permanent controlled markings on face of receptacle compliant with ASHRAE 90.1, CA Title 24, and NEC.

Auto-ground clip assures positive ground.

Half-controlled versions include welded, pre-wired lead that control top half of receptacle for split circuit applications.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

| | | | |
|-------------------|----------------|-------|------|
| Product Line | Pass & Seymour | Color | Gray |
| Country Of Origin | Mexico | | |

Dimensions

| | | | |
|-------------------|---------|------------------|----------|
| Product Width US | 1.5 in | Product Depth US | 0.625 in |
| Product Height US | 2.75 in | | |

Listing Agencies / 3rd Party Agencies

cULus Listed

Yes

Technical Information

Amperage

15 A
