



Pass and Seymour  
PlugTail® Connectors, Right Angle, Stranded, XHHW Black Blue, 6"  
Part No. PTR6STRXBB



PlugTail® Connectors, Right Angle, Stranded, XHHW Black Blue, 6-inch

### Features & Benefits

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.	Large brass contacts snugly terminate on device blade terminals.
Pre-stripped connector leads fasten to conductors, easier than standard pigtails.	Available in any wire length up to 25 inches, use Configurable Solutions to order.
NAFTA-Compliant	Uses #12 AWG stranded XHHW wire
Ideal for applications with low leakage current requirements	For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .
For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, <a href="#">click here</a> .	

### Specifications

#### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
--------------	----------------	-------------------	--------

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----