



Pass and Seymour  
**PlugTail® Hospital-Grade 15A USB Charging Receptacles, Black**  
Part No. PTTR15HACUSBBK



PlugTail® Hospital Grade USB Charging Receptacles provide the convenience of mobile charging without the need for a bulky AC adapter. This device is a perfect match for the constant needs of today's mobile environment and is rugged enough to withstand hard-use commercial applications. It comes equipped with two UL Fed Spec AC receptacles and two USB charging ports for mobile devices: one Type-A port and one Type-C port for newer products. An efficient, 15.5W power supply provides the power needed for charging mobile phones and tablets. The PlugTail® termination provides a more productive, secure, and safer installation and allows you to connect with the future of wiring device innovations. For detailed PlugTail® information, visit our PlugTail® Headquarters.

## Features & Benefits

AC receptacles are tamper resistant as standard : patented shutter system prevents improper insertion of foreign objects	Efficient, 15.5W power supply for fast charging of mobile phones and tablets
Triple-wipe, brass line contacts for 15A commercial applications	Multiple color options available
Zinc-plated steel for corrosion resistance	5Vdc Type-C USB port to charge USB Type-C compatible mobile devices
PlugTail termination allows for more productive, finger-safe installation and added future flexibility	Stainless steel auto-ground clips assure positive ground
Available in 15 & 20A, Specification Grade and Hospital Grade configurations	

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	China		

### Dimensions

Product Width US	1.693 in	Product Depth US	1.45 in
Product Height US	2.677 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

Technical Information

USB Amperage	3.1 A	Number of USBs	2
USB Power Output	15 W	Amperage	15 A

---