



PlugTail® Split Circuit Tamper-Resistant Decorator Spec Grade Receptacle, 15A, 125V PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

### Features & Benefits

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications.
- No exposed terminals create a finger safe application before, during, and after installation.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Auto-ground clip assures positive ground.

### Specifications

#### General Info

Product Line	Pass & Seymour	Replaced by Part Number	TR26262BK
Color	Black	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor, Tamper-Resistant
Type	Outlet		

#### Dimensions

Product Width US	1.5 in	Product Depth US	0.875 in
Product Height US	2.75 in		

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Voltage	125.0 V		