




radiant Collection
radiant® Single-Pole 3-Way Vacancy Sensor, Tri-Color
Part No. RRW600VTC



Never worry about leaving the lights on, with the radiant Registered Vacancy Sensor. It automatically shuts off when a room is empty, and includes an adjustable delay setting of up to 20 minutes to match your needs. Designed for ease and style, it features a built-in locator light, and the sleek, clean lines of radiant Registered for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.

Features & Benefits

Works with various lights/bulbs, including: Incandescent, LED, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp.

Turn the light on when you enter, and let it turn itself off automatically after you leave for true convenience.

Features an adjustable time delay, letting you set the automatic shut-off after a specified window of time. Delay settings range from 30 seconds to 20 minutes after the room is vacated.

Installs easily in place of a standard light or fan (single-pole) switch. No neutral wire required.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

The secret for always turning the lights off? A device that does it for you automatically. Perfect for bathrooms, hallways, closets, and garages.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Features	Motion Sensor	Switch Type	Motion Sensor
Application Sector	Residential	Standard	cULus

Dimensions

Product Width US	1.69 in	Product Depth US	1.88 in
Product Height US	2.63 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Target Size	180 deg	Response Frequency	60 Hz
Sensor Type	Occupancy	Number of Poles	Single Pole
Mounting Type	Box	Sensing Range	600 sq ft
Sensitivity	60Hz	Load	120VAC
Environmental Conditions	Indoor Use Only		
