



Pass and Seymour
Replacement Switch, 60A
Part No. RS60



60As Replacement Switch

Specifications

General Info

Product Line	Pass & Seymour	Color	Blue
Country Of Origin	Germany	Application Sector	Industrial
Standard	UL, CSA		

Dimensions

Product Width US	7.3 in	Product Depth US	7.1 in
Product Height US	11.6 in		

Listing Agencies / 3rd Party Agencies

cUL Listed	Yes
------------	-----

Technical Information

Contact Configuration	(Optional) 1 N.O. & 1 N.C.	Contact Rating	(Optional) 10A @ 600VAC
Amperage	60 A	Voltage	600.0 V
Environmental Conditions	Moisture Resistance: Per UL50, Section 35, NEMA Enclosure Type 4X (watertight, hosedown), Type 12K (dusttight, falling dirt), and IP67 suitability: Flammability: UL94 5VA and V0 Classification: UV Resistance: All enclosure materials are UV stable		