



## Features & Benefits

Tough, impact-resistant thermoplastic housing.	Matches appearance of standard P&S toggle switch.
Uses conventional 3-way wiring when used in conjunction with a 3-way switch.	Specially designed capacitive circuitry to virtually eliminate fan motor "hum".

## Specifications

General Info			
Product Line	Pass & Seymour	Replaced by Part Number	TSDFB83PBK
Color	Black	Country Of Origin	China
Application Sector	Residential/Commercial	Standard	cULus, RoHS
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Amperage	8 A	Voltage	120.0 V
Load	Fluorescent	Environmental Conditions	Humidity: Less than 95% non condensing