



Pass and Seymour  
20A 125V Tamper-Resistant Duplex Receptacle with USB A/C Charging Ports, Nickel  
Part No. TR20USBACNI



20A 125A Duplex Tamper-Resistant REC + USBA USBC 3.1A

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Nickel
Country Of Origin	China		

### Dimensions

Product Width US	1.693 in	Product Depth US	1.425 in
Product Height US	2.677 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

### Technical Information

USB Amperage	3.1 A	Number of USBs	2
USB Power Output	15 W	Amperage	20 A