



Pass and Seymour
Discontinued - Hospital-Grade USB Charger with Tamper-Resistant 15A Duplex Receptacles, Gray
Part No. TR8200HUSBGRY



Features & Benefits

- Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices
 - AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects.
 - Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire.
 - AC receptacles available in 15 and 20 Amp, 125V
 - Multiple color options available.
 - Stainless steel auto-ground clips assure positive ground.
- For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	TR15HUSBAC6GRY
Color	Gray	Country Of Origin	China

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Is Tamper-Resistant	Yes	USB Amperage	3.1 A
Number of USBs	2	USB Power Output	15 W

Amperage

15 A
