



**Wattstopper**  
**Digital Time Switch, 24VAC, Black**  
Part No. TS-400-24-B



The IntelliSwitch TS-400 series digital time switches automatically turn lights off after a preset time. The simple pushbutton operation provides users with convenient time out lighting control without the nuisance of twist timers.

## Features & Benefits

Automatically turns lights off after preset time

Optional audible or visual alerts before lights turn off

Digital operation and simple pushbutton set-up

Bright electroluminescent LCD shows timer's countdown

Terminal style wiring for simplified installation

Time scroll features allows timer to adjust up or down

## Specifications

### General Info

|                    |                       |                   |        |
|--------------------|-----------------------|-------------------|--------|
| Product Line       | Wattstopper           | Color             | Black  |
| UPC Number         | 754182913770          | Country Of Origin | China  |
| Features           | Single Display, Timer | Switch Type       | Push   |
| Application Sector | Commercial            | Warranty Type     | 5-Year |

### Dimensions

|                   |            |                   |         |
|-------------------|------------|-------------------|---------|
| Product Width US  | 3.0 in     | Product Weight US | 0.35 lb |
| Product Volume US | 37.5 cu in | Product Depth US  | 5.0 in  |
| Product Height US | 2.5 in     |                   |         |

### Additional Information

|                 |     |                                          |     |
|-----------------|-----|------------------------------------------|-----|
| RoHS Conformant | Yes | DesignLights Consortium Qualified System | Yes |
|-----------------|-----|------------------------------------------|-----|

|                       |                      |          |        |
|-----------------------|----------------------|----------|--------|
| Security              | Yes                  |          |        |
| Technical Information |                      |          |        |
| Number of Buttons     | 1                    | Amperage | 41 mA  |
| Timing Range          | 5 minutes - 12 hours | Voltage  | 24.0 V |
| Connection Type       | Wired                |          |        |