



Wiremold  
Plug-In Outlet Center Unit / 120V/15A/48 long/16 O/L /lighted switch/6' cord  
Part No. UL402BC



Sixteen outlets, lighted switch, rugged gray aluminum housing, 15A, 6' (1.8m) 14/3 SJT black cord with NEMA5-15 plug. Length 48" (1.2m). Receptacle center-to-center 2 1/2" (64mm). Snap-on, slide-off mounting.

Features & Benefits

Sixteen outlets, lighted switch, rugged gray aluminum housing, 15A, 6' (1.8m) 14/3 SJT black cord with NEMA5-15 plug. Length 48" (1.2m). Receptacle center-to-center 2 1/2" (64mm). Snap-on, slide-off mounting.

Specifications

General Info

|                       |   |                    |              |
|-----------------------|---|--------------------|--------------|
| Product Line          | Wiremold  | UPC Number         | 786776047776 |
| Country Of Origin     | Mexico  | Receptacle Type    | Simplex      |
| Number of Receptacles | 16  | Application Sector | Commercial   |
| Standard              | cULus Recognized: File E66421 Guide<br>XBYS XUHT VZCA | Type               | PIOC         |

Dimensions

|                  |        |                   |         |
|------------------|--------|-------------------|---------|
| Product Width US | 1.5 in | Product Length US | 48.0 in |
|------------------|--------|-------------------|---------|

Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E66421 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Buy American Act Compliance

|       |     |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

---

Additional Information

---

|                 |     |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

---

Technical Information

---

|       |        |                  |       |
|-------|--------|------------------|-------|
| Phase | Single | Frequency Rating | 60 Hz |
|-------|--------|------------------|-------|

---

|          |      |                |          |
|----------|------|----------------|----------|
| Amperage | 15 A | Enclosure Type | Aluminum |
|----------|------|----------------|----------|

---

|               |                    |         |         |
|---------------|--------------------|---------|---------|
| Mounting Type | Snap-on, Slide-off | Voltage | 125.0 V |
|---------------|--------------------|---------|---------|

---

|                          |                        |
|--------------------------|------------------------|
| Environmental Conditions | Dry interior locations |
|--------------------------|------------------------|

---