



Wiremold
5' All USB Steel Plugmold® Multioutlet System
Part No. V20USB512



5' (1.5m) length with 12" spacing. USB is 2.4 Amps (shared between two ports) 5VDC. .040" (1.0mm) steel housing. Packed two per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. Each USB module provides 2 ports with 2.4 Amps of shared charging. Please note the charging load on one module will not affect the charging performance of the other USB modules in the product.

Features & Benefits

USB charging. Dual-port charging modules share 2.4 amps of charging capacity and can charge multiple phones, tablets or other mobile devices at the same time.

Compact design. Low-profile design installs in tight locations while offering multiple USB charging connections. Receptacle spacing accommodates bulky AC adapters.

Multiple colors and finishes. Painted finishes of black, gray, ivory, and white, as well as stainless steel versions integrate easily with any room decor.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776184396
Country Of Origin	United States	Number of Receptacles	5
Application Sector	Commercial	Standard	cULus Listed Multioutlet Assembly: File E15191 Guide PVGT
Type	Plugmold		

Dimensions

Product Width US	1.3 in	Product Depth US	0.75 in
Product Length US	1.3 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Frequency Rating	60 Hz	Amperage	20 A
Enclosure Type	Steel	Voltage	125.0 V
Environmental Conditions	Dry interior locations		