



Wattstopper
Wattstopper PLUS Pre-Terminated Greenbus Cable, 20 ft
Part No. BCS_WA_EN-PTC-20FT-GB2

The EN-PTC-20FT-GB2 is a 20ft jumper of Greenbus cable. The cable comes pre-terminated with Greenbus connectors to allow quick installation.



Features & Benefits

Cost-effective wired solutions for seamless lighting controls

Integrates a range of devices (load controllers, occupancy sensors, and wallstations) into a complete solution

Allows electrical contractors to quickly verify wiring installations and obtain occupancy permits

Specifications

General Info

Product Line	Wattstopper	Color	White
UPC Number	840356701653	Country Of Origin	United States
Jacket Color	White	Application Sector	Commercial
Warranty Type	5-Year	Type	Cable

Dimensions

Product Length US	20.0 FT	Cable Length	20 ft
-------------------	---------	--------------	-------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

Technical Information

Jacket Material	PVC	Operating Temperature Min	-10 °C
Compatibility	GreenBus, Wattstopper PLUS	Wire Gauge	18 AWG
Jacket Application	Plenum Rated	Bend Radius	10 mm
Shielded/Unshielded	Unshielded	Termination Style	Pre-Terminated
Conductor	2-Wire	Operating Temperature Max	75 °C
Jacket Rating	CMP Rated	Cable Diameter	0.1 in
Indoor/Outdoor	Indoor	Operating Temperature	-10°-75°C
Operating Humidity	0-95% RH (Non-Condensing)	Insulation Material	PVC
